



MASTERLine ES

MASTERL ES 45W GU5.3 12V 8D 1CT/4X5F

Low-voltage halogen burner with very high energy efficiency and long lifetime thanks to IRR coating in glass reflector. Ideal solution for small decorative luminaires, putting your objects in the spotlight. Dichroic coating prevents heat transmission onto the object.


Product data

General Information	
Cap-Base	GU5.3 [GU5.3]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	5,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	5,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Beam Angle (Nom)	8 degree(s)
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	100
Luminous Flux in 90° Cone (Rated)	625 lm
Operating and Electrical	
Power Consumption	45.0 W
Lamp Current (Nom)	3.75 A
Starting Time (Nom)	0.0 s
Warm-up time to 60° light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	12 V
Voltage (Nom)	12 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	MR16 [2inch/50mm]
Approval and Application	
Energy Consumption kWh/1000 h	48 kWh
Product Data	
Order product name	MASTERL ES 45W GU5.3 12V 8D 1CT/4X5F
Full product name	MASTERL ES 45W GU5.3 12V 8D 1CT/4X5F
Full product code	871150042438971
Order code	924895917101
Material Nr. (12NC)	924895917101
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500424389
Numerator - Packs per outer box	20
EAN/UPC - Case	8711500410221


MASTERLine ES

Dimensional drawing



Product	D (max)	C1 (max)
MASTERL ES 45W GU5.3 12V 8D 1CT/4X5F	51 mm	50.5 mm

Photometric data



Light Distribution Diagram - MASTERL ES 45W GU5.3 12V 8D 1CT/4X5F

