

MASTERCapsule

MASTERCaps 30W GY6.35 12V IR 1CT/5X10F

Low-voltage halogen capsule with very high energy efficiency and long lifetime thanks to IRR coating. Ideal solution for small decorative luminaires. UV-block glass and low-pressure filling allow usage without cover glass.

Product data

| General Information | |
|------------------------|----------------------------------|
| Cap-Base | GY6.35 [GY6.35] |
| Operating Position | UNIVERSAL [Any or Universal (U)] |
| Nominal lifetime | 4,000 hour(s) |
| Switching Cycle | 16,000 |
| Rated Lifetime (Hours) | 4,000 hour(s) |
| Lighting Technology | Halogen |

| Light Technical | |
|------------------------------------|---------|
| Luminous Flux | 750 lm |
| Correlated Color Temperature (Nom) | 3000 K |
| Luminous Efficacy (rated) (Nom) | 23 lm/W |
| Color rendering index (CRI) | 100 |

| Operating and Electrical | |
|---------------------------|----------------------|
| Power Consumption | 30.0 W |
| Lamp Current (Nom) | 2.5 A |
| Starting Time (Nom) | 0.0 s |
| Warm-up time to 60% light | instant full light s |
| Power Factor (Fraction) | 1 |
| Voltage (Nom) | 12 V |
| Voltage (Nom) | 12 V |

| Controls and Dimming | |
|----------------------|-----|
| Dimmable | Yes |


| Mechanical and Housing | |
|------------------------|--------------|
| Bulb Finish | IR Coated |
| Bulb Shape | T11 [T 11mm] |

| Approval and Application | |
|-------------------------------|--------|
| Energy Consumption kWh/1000 h | 32 kWh |

| Product Data | |
|---------------------------------|--|
| Order product name | MASTERCaps 30W GY6.35 12V IR 1CT/5X10F |
| Full product name | MASTERCaps 30W GY6.35 12V IR 1CT/5X10F |
| Full product code | 872790020354770 |
| Order code | 924898317102 |
| Material Nr. (12NC) | 924898317102 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8727900203547 |
| Numerator - Packs per outer box | 50 |
| EAN/UPC - Case | 8727900203905 |

MASTERCapsule

Dimensional drawing



| Product | D (max) | L | C (max) |
|--|---------|-------|---------|
| MASTERCaps 30W GY6.35 12V IR 1CT/5X10F | 12 mm | 30 mm | 44 mm |

