



# DuraMax Reflector Flood

## 45R20/LL 120V 6/1 TP

Philips DuraMax® Long Life Reflector Flood Bulbs reduce the hassle of replacing light bulbs every few months, since all DuraMax products last longer than standard incandescent light bulbs. Available in a variety of sizes and wattages. Use flood lights for general or ambient lighting; use spot lights to highlight artwork or architecture. Both are ideal for use in recessed cans or track lighting fixtures.

### Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Rated Lifetime (Hours)	2,500 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	385 lm
Operating and Electrical	
Power Consumption	45 W
Voltage (Nom)	120 V
Voltage (Nom)	120 V
Mechanical and Housing	
Bulb Finish	Frosted

Bulb Shape	R20 [R 63mm]
Product Data	
Order product name	45R20/LL 120V 6/1 TP
Full product name	45R20/LL 120V 6/1 TP
Order code	925154636310
Material Nr. (12NC)	925154636310
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677203238
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677433494

# DuraMax Reflector Flood

## Dimensional drawing

Product	D	C (max)
45R20/LL 120V 6/1 TP	2.5 inch	3.94 inch

