



Reflector Flood

65BR40/FL 130V 12/1 PRO

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. These flood lamps produce homogeneous beams of high intensity for general illumination.


Product data

General Information	
Base	E26 [Single Contact Medium Screw]
Operating Position	Universal [Universal]
Main Application	Flood and Ambient Lighting
Gas Filling	GAS
Life with 3 Hour Per Day Use	1.8 a
Light Technical	
Beam Angle (Nom)	55 °
Initial lumen (Nom)	565 lm
Beam Description	Flood [Flood]
Luminous Flux Lamp @ 120V	425 lm
Correlated Color Temperature (Nom)	2750 K
Operating and Electrical	
Power (Rated) (Nom)	65 W
Lamp Wattage Rated@120V	55 W
Voltage (Nom)	130 V

Mechanical and Housing	
Bulb Finish	Clear (CL)
Cap-Base Information	Aluminium [Aluminium Cap]
Filament Shape	CC6 [Straight]
Approval and Application	
Estimated Energy Cost Per Year at 120V	6.67 S
Estimated Energy Cost Per Year	7.83 S
Product Data	
Order product name	65BR40/FL 130V 12/1 PRO
EAN/UPC - Product	046677140083
Order code	140087
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	925184436105
Net Weight (Piece)	0.001 kg

Reflector Flood

Dimensional drawing



Product

65BR40/FL 130V 12/1 PRO

65W E26 130V BR40 FL CL

