



# Reflector Flood

## 65BR30/FL 130V 12/1 PRO

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. These flood lamps produce homogeneous beams of high intensity for general illumination.


### Product data

General Information	
Base	E26 [ Single Contact Medium Screw]
Operating Position	Universal [ Universal]
Main Application	Indoor Reflector
Gas Filling	GAS
Life with 3 Hour Per Day Use	1.8 a
Light Technical	
Beam Angle (Nom)	300 °
Initial lumen (Nom)	605 lm
Beam Description	Flood [ Flood]
Luminous Flux Lamp @ 120V	450 lm
Correlated Color Temperature (Nom)	2680 K
Operating and Electrical	
Power (Rated) (Nom)	65 W
Lamp Wattage Rated@120V	55 W
Voltage (Nom)	130 V

Mechanical and Housing	
Bulb Finish	Frosted (FR)
Cap-Base Information	Aluminium [ Aluminium Cap]
Filament Shape	CC6 [ Straight]
Approval and Application	
Estimated Energy Cost Per Year at 120V	6.67 S
Estimated Energy Cost Per Year	7.83 S
Product Data	
Order product name	65BR30/FL 130V 12/1 PRO
EAN/UPC - Product	046677140076
Order code	140079
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	925190336106
Net Weight (Piece)	0.001 kg

## Reflector Flood

### Dimensional drawing



#### Product

65BR30/FL 130V 12/1 PRO

65W E26 130V BR30 FR

