



# DuraMax Deco Bent Tip

## BC40BA9-1/2/CL/LL 6/2 TP

Philips DuraMax® Long Life Decorative bent tip bulbs reduce the hassle of replacing light bulbs every few months, since all DuraMax products last longer than standard incandescent light bulbs. Philips Duramax decorative bent tip bulbs are available in a variety of wattages with clear and frost finishes. The clear bulbs provide decorative sparkle, while the frost bulbs add a soft glow to add a pleasant touch to home decor.

### Product data

| General Information |  |
|---------------------|--|
| Base                | E26 [ Single Contact Medium Screw]       |
| Operating Position  | Base Down +/- 90 D [ Base Down +/- 90 D] |
| Main Application    | Decorative                               |
| Gas Filling         | GAS                                      |

| Light Technical     |        |
|---------------------|--------|
| Initial lumen (Nom) | 300 lm |

| Operating and Electrical |       |
|--------------------------|-------|
| Power (Rated) (Nom)      | 40 W  |
| Voltage (Nom)            | 120 V |

| Mechanical and Housing |       |
|------------------------|-------|
| Bulb Finish            | Clear |

|                      |                            |
|----------------------|----------------------------|
| Cap-Base Information | Aluminium [ Aluminium Cap] |
| Filament Shape       | C-7A [ Ring]               |


| Product Data                    |                          |
|---------------------------------|--------------------------|
| Order product name              | BC40BA9-1/2/CL/LL 6/2 TP |
| EAN/UPC - Product               | 50046677168204           |
| Order code                      | 168203                   |
| Numerator - Quantity Per Pack   | 1                        |
| Numerator - Packs per outer box | 6                        |
| Material Nr. (12NC)             | 925240536308             |
| Net Weight (Piece)              | 0.500 g                  |

## DuraMax Deco Bent Tip

### Dimensional drawing

#### Product

BC40BA9-1/2/CL/LL 6/2 TP



40W E26 120V BA9 1/2 CL

