



# Industrial Service

## 150A/35RS/BR 120/130V 60PK


Philips Econ-o-watt® Industrial Service Lamps can directly replace standard life incandescent lamps, offering instant energy savings for many applications.

### Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	3,500 hour(s)
Rated Lifetime (Hours)	3,500 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	1,640 lumen
Operating and Electrical	
Power Consumption	150 W
Starting Time (Nom)	0.0 s
Voltage (Nom)	120-130 V

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	A21 [A 21mm]
Product Data	
Order product name	150A/35RS/BR 120/130V 60PK
Order code	925246934302
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	60
Material Nr. (12NC)	925246934302
Full product name	150A/35RS/BR 120/130V 60PK
EAN/UPC - Case	50046677275889
EAN/UPC - Product/Case	046677275884

Dimensional drawing



Product
150A/35RS/BR 120/130V 60PK

