



Rough / Vibration Service

200PS30/23 120/130V 60/1


Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. Rough Service incandescent lamps have an exceptionally strong filament for which a special filament wire is used, which makes these lamps extremely suitable for places where shocks, bumps and vibrations frequently occur. The clear version, with its completely visible filament, is a brilliant light source, whereas the inside-frosted lamp is used wherever well diffused light is required.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux (Max)	2,670 lumen
Luminous Flux	3,500 lumen
Operating and Electrical	
Power Consumption	200 W
Voltage (Nom)	120-130 V
Mechanical and Housing	
Bulb Finish	Frosted

Bulb Shape	PS30
Product Data	
Order product name	200PS30/23 120/130V 60/1
Order code	925266836102
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	60
Material Nr. (12NC)	925266836102
Full product name	200PS30/23 120/130V 60/1
EAN/UPC - Case	50046677143041
EAN/UPC - Product/Case	046677143046

Dimensional drawing



Product
200PS30/23 120/130V 60/1

