



Mini Reflector

BC-40R14

Philips Family of Mini Reflector bulbs provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	S90 [Standing +/-90D or Base Down (BDH)]
Rated Lifetime (Hours)	1,500 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	250 lumen
Operating and Electrical	
Power Consumption	40 W
Voltage (Nom)	120 V
Voltage (Nom)	120 V
Mechanical and Housing	
Bulb Finish	Frosted

Bulb Shape	R14
Product Data	
Order product name	BC-40R14
Order code	925270936303
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	925270936303
Full product name	BC-40R14
EAN/UPC - Case	50067805010264
EAN/UPC - Product/Case	067805010269

Mini Reflector

Dimensional drawing

Product	D	C (max)
BC-40R14	1.75 inch	2.625 inch

