



Rough / Vibration Service

100A/2P/RS 12/2


Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. Rough Service incandescent lamps have an exceptionally strong filament for which a special filament wire is used, which makes these lamps extremely suitable for places where shocks, bumps and vibrations frequently occur. The clear version, with its completely visible filament, is a brilliant light source, whereas the inside-frosted lamp is used wherever well diffused light is required.

Product data

| General Information | |
|--------------------------|-----------------------------------|
| Cap-Base | E26 [Single Contact Medium Screw] |
| Operating Position | UNIVERSAL [Any or Universal (U)] |
| Rated Lifetime (Hours) | 2,000 hour(s) |
| Lighting Technology | Incandescent |
| Operating and Electrical | |
| Power Consumption | 100 W |
| Voltage (Nom) | 130 V |
| Voltage (Nom) | 130 V |
| Mechanical and Housing | |
| Bulb Finish | Frosted |

| Bulb Shape | A19 [A 19mm] |
|---------------------------------|-----------------|
| Product Data | |
| Order product name | 100A/2P/RS 12/2 |
| Full product name | 100A/2P/RS 12/2 |
| Order code | 111724 |
| Material Nr. (12NC) | 925283534304 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 046677286903 |
| Numerator - Packs per outer box | 12 |
| EAN/UPC - Case | 50046677286908 |

Dimensional drawing



A19

| Product | D | C (max) |
|-----------------|------------|------------|
| 100A/2P/RS 12/2 | 2.375 inch | 4.438 inch |

