



Silicone Coated Rough Service

100A/RS/TF 120-130V 60PK

The Philips Family of Silicone Coated Rough Service bulbs are the perfect choice in areas where there is concern if a bulb drops or shatters. Since Silicone Coated Rough Service bulbs resist breakage or shattering, they are perfect for food serving areas, as well as, standard, industrial rough surface, appliance and sign use.

Product data

General Information	
Base	E26 [Single Contact Medium Screw]
Operating Position	Universal [Universal]
Main Application	Rough Service (RS)
Gas Filling	GAS
Nominal Lifetime (Nom)	1000 h
Footnote Incandescent 1	Silicone Coating reduces lumen output from Standard Values less than 3%. (66)

Light Technical	
Initial lumen (Nom)	1050 lm
Luminous Flux (Rated) (Nom)	1050 lm


Operating and Electrical	
Power (Rated) (Nom)	100 W
Starting Time (Nom)	0.0 s
Voltage (Nom)	120-130 V

Mechanical and Housing	
Bulb Finish	Frost Silicone
Cap-Base Information	Aluminium [Aluminium Cap]
Filament Shape	Reinforced Construction [Reinforced]

Product Data	
Order product name	100A/RS/TF 120-130V 60PK
EAN/UPC - Product	046677279851
Order code	149716
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	60
Material Nr. (12NC)	925286736303
Net Weight (Piece)	0.001 kg

Silicone Coated Rough Service

Dimensional drawing



A21

Product

100A/RS/TF 120-130V 60PK

RC 100W E26 120-130V A-21 FR-Sil

