



Plusline Small

PLUS PRO S 500W R7s 230V 1CT/50

Mains-voltage linear lamp giving white halogen light


Product data

General Information	
Cap base	R7S [R7s]
Burning Position	UNIVERSAL [Any/Universal]
Nominal lifetime (nom.)	2000 h
Light Technical	
Lamp Luminous Flux 25°C EL (Nom)	9900 lm
Colour Temperature, horizontal (Nom)	2900 K
Lamp Luminous Efficacy EM (Nom)	19.8 lm/W
Colour Rendering Index, horiz (Nom)	100
Operating and Electrical	
Power (Rated) (Nom)	500.0 W
Lamp current (nom.)	2.17 A
Starting time (nom.)	0.0 s
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	yes
Mechanical and Housing	
Bulb finish	Clear (CL)

Approval and Application	
Energy efficiency label (EEL)	D
Luminaire Design Requirements	
Bulb temperature (max.)	900 °C
Pinch temperature (max.)	350 °C
Product Data	
Full product code	871829114776300
Order product name	PLUS PRO S 500W R7s 230V 1CT/50
EAN/UPC – product	8718291147763
Order code	925632544211
Numerator – quantity per pack	1
Numerator – packs per outer box	50
Material no. (12NC)	925632544211
Net weight (piece)	0.009 kg
ILCOS Code	HDG//RS-500-230-R7s-117

Plusline Small

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
PLUS PRO S 500W R7s 230V 1CT/50	12 mm	115.8 mm	114.2 mm	112.6 mm	117.6 mm

DESmall 500W R7s 230V T11 CL

