



Plusline Small

PLUS PRO S 500W R7s 230V 1CT/50

Mains-voltage linear lamp giving white halogen light


Product data

Informasi Umum	
Tutup-Dasar	R7s
Posisi Pengoperasian	UNIVERSAL [Setiap atau Universal (U)]
Nominal masa pakai	2.000 jam
Nilai Masa Pakai (Jam)	2.000 jam
Teknologi Pencahayaan	Halogen
Teknis Lampu	
Flux Cahaya	9.900 lm
Suhu Warna Terkorelasi (Nom)	2900 K
Daya Penerangan (terukur) (Nom)	19,8 lm/W
Indeks renderasi warna (CRI)	100
Pengoperasian dan Kelistrikan	
Konsumsi Daya	500,0 W
Arus Lampu (Nom)	2,17 A
Waktu Mulai (Nom)	0,0 s
Tegangan (Nom)	230 V
Tegangan (Nom)	230 V

Kontrol dan Peredupan	
Dapat diredupkan	Ya
Mekanis dan Housing	
Lapisan bohlam	Bening
Bentuk Bohlam	T11 [T 11 mm]
Data Produk	
Nama produk pesanan	PLUS PRO S 500W R7s 230V 1CT/50
Nama lengkap produk	PLUS PRO S 500W R7s 230V 1CT/50
Kode produk lengkap	871829114776300
Kode urutan	925632544211
No. Material (12NC)	925632544211
Numerator - Jumlah Per Pak	1
EAN/UPC - Produk/Kantung	8718291147763
Numerator - Pak per kotak bagian luar	50
EAN/UPC - Kantung	8718291147770

Plusline Small

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
PLUS PRO S 500W R7s 230V 1CT/50	12 mm	115,8 mm	114,2 mm	112,6 mm	117,6 mm

