



# Halogen Classic Candle B35

## ClassicHalogen28W E14 240V B35 CL 1CT/15

Philips Halogen Classic Candle light bulbs offer the classical shape you are used to. This new 'classic' gives high-quality light, is dimmable and starts immediately.

### Product data

General information	
Cap base	E14 [ E14]
Operating position	UNIVERSAL [ Any or Universal (U)]
Nominal lifetime (nom.)	2000 h
Switching cycle	8,000X
Rated lifetime (hours)	2000 h
Light technical	
Luminous flux (nom.)	370 lm
Luminous flux (rated) (nom.)	370 lm
Correlated Colour Temperature (Nom)	2800 K
Luminous efficacy (rated) (nom.)	12.4 lm/W
Colour rendering index (nom.)	100
LLMF at end of nominal lifetime (min.)	80 %
Operating and electrical	
Power (Rated) (Nom)	28.0 W
Lamp current (nom.)	0.12 A
Starting time (nom.)	0.0 s
Warm-up time to 60% light (nom.)	instant full light
Power factor (nom.)	1

Voltage (Nom)	240 V
Controls and dimming	
Dimmable	Yes
Mechanical and housing	
Lamp Finish	Clear
Bulb shape	B35 [ B 35mm]
Approval and application	
Energy consumption kWh/1,000 hours	28 kWh
Luminaire design requirements	
Cap-base temperature (max.)	130 °C
Cap-base temperature (max.)	266 °F
Product data	
Full product code	871829112275300
Order product name	ClassicHalogen28W E14 240V B35 CL 1CT/15
EAN/UPC – product	8718291122753
Order code	12275300
SAP numerator – quantity per pack	1

## Halogen Classic Candle B35

Numerator – packs per outer box	15
SAP material	925639645503
Net Weight (Piece)	18.400 g

### Dimensional drawing



Product	D (max)	C (max)
ClassicHalogen28W E14 240V B35 CL 1CT/15	36 mm	99.2 mm

ClassicHalogen28W E14 240V B35 CL 1CT/15

