



# Halogen Classic Candle B35

## ClassicHalo 28W B22 240V B35 CL 2PF/10x7

Philips Halogen Classic Candle light bulbs offer the classical shape you are used to. This new 'classic' gives high-quality light, is dimmable and starts immediately.


### Product data

General Information	
Cap-Base	B22 [B22]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Luminous Flux	370 lm
Correlated Color Temperature (Nom)	2800 K
Luminous Efficacy (rated) (Nom)	12.4 lm/W
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	28.0 W
Lamp Current (Nom)	0.12 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	240 V
Voltage (Nom)	240 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	B35 [B 35mm]
Approval and Application	
Energy Consumption kWh/1000 h	28 kWh
Product Data	
Order product name	ClassicHalo 28W B22 240V B35 CL 2PF/10x7
Full product name	ClassicHalo 28W B22 240V B35 CL 2PF/10x7
Full product code	871829121960600
Order code	925639845505
Material Nr. (12NC)	925639845505
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291219606
Numerator - Packs per outer box	70
EAN/UPC - Case	8718291219620

# Halogen Classic Candle B35

## Dimensional drawing



Product	D (max)	C (max)
ClassicHalo 28W B22 240V B35 CL 2PF/10x7	36 mm	94.5 mm

