



# Halogen Clickline G9

## Halogen MV Caps 28W G9 230V CL 1BC/10

Ideal solution for small decorative luminaires. UV-block glass and safety fuse allow usage without cover glass. The compact Clickline gives crisp white light over a long lifetime.


### Product data

General Information	
Cap-Base	G9
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Luminous Flux	370 lm
Correlated Color Temperature (Nom)	2800 K
Luminous Efficacy (rated) (Nom)	12.1 lm/W
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	28.0 W
Lamp Current (Nom)	0.12 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	230 V
Voltage (Nom)	230 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T13
Approval and Application	
Energy Consumption kWh/1000 h	28 kWh
Product Data	
Order product name	Halogen MV Caps 28W G9 230V CL 1BC/10
Full product name	Halogen MV Caps 28W G9 230V CL 1BC/10
Full product code	872790025287325
Order code	925640644202
Material Nr. (12NC)	925640644202
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900252873
Numerator - Packs per outer box	10
EAN/UPC - Case	8727900662191

# Halogen Clickline G9

## Dimensional drawing



Product	D (max)	L	C (max)
Halogen MV Caps 28W G9 230V CL 1BC/10	13 mm	21.7 mm	45 mm

