



Halogen Clickline G9

Halogen MV Click 42W G9 230V CL 1CT

Ideal solution for small decorative luminaires. UV-block glass and safety fuse allow usage without cover glass. The compact Clickline gives crisp white light over a long lifetime.

Product data

General information	
Cap base	G9 [G9]
Operating position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime (nom.)	2000 h
Switching cycle	8,000X
Rated lifetime (hours)	2000 h
	Sphere

Light technical	
Luminous flux (nom.)	590 lm
Luminous flux (rated) (nom.)	630 lm
Chromaticity coordinate X (nom.)	0.452
Chromaticity coordinate Y (nom.)	0.409
Correlated Colour Temperature (Nom)	2800 K
Luminous efficacy (rated) (nom.)	15 lm/W
Colour rendering index (nom.)	100
LLMF at end of nominal lifetime (min.)	80 %

Operating and electrical	
Power (Rated) (Nom)	44 W
Lamp current (nom.)	0.18 A
Starting time (nom.)	0.0 s
Warm-up time to 60% light (nom.)	instant full light
Power factor (nom.)	1

Voltage (Nom)	230 V
Controls and dimming	
Dimmable	Yes
Mechanical and housing	
Lamp Finish	Clear
Bulb shape	T13 [T 13 mm]

Approval and application	
Energy Efficiency Class	G
Energy consumption kWh/1,000 hours	44 kWh
	423238

Luminaire design requirements	
Bulb temperature (max.)	950 °C
Pinch temperature (max.)	350 °C
Pinch temperature (max.)	350 °C


Product data	
Full product code	872790086401400
Order product name	Halogen MV Click 42W G9 230V CL 1CT
EAN/UPC – product	8727900864014
Order code	86401400

Halogen Clickline G9

SAP numerator – quantity per pack	1
Numerator – packs per outer box	100
SAP material	925640844205

Net Weight (Piece)	0.003 kg
--------------------	----------

Dimensional drawing



Product	D (max)	L	C (max)
Halogen MV Click 42W G9 230V CL 1CT	13 mm	21.7 mm	45 mm

Halogen MV Click 42W G9 230V CL 1CT

