



Essential MV MR16 Alu

ESS MR16 Alu 50W GU10 230V 36D 1CT

The Essential MV MR16 Alu is part of the Philips "Value for Money" ranges. It is ideal for professional end-users looking for accent light - without a transformer - to create contrast in shops, hotels and restaurants.


Product data

General Information	
Cap-Base	GU10 [GU10]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Beam Angle (Nom)	36 degree(s)
Correlated Color Temperature (Nom)	2800 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	50 W
Starting Time (Nom)	0.0 s
Voltage (Nom)	230 V
Voltage (Nom)	230 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	MR16 [2inch/50mm]
Product Data	
Order product name	ESS MR16 Alu 50W GU10 230V 36D 1CT
Full product name	ESS MR16 Alu 50W GU10 230V 36D 1CT
Full product code	871829119517700
Order code	925644344203
Material Nr. (12NC)	925644344203
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291195177
Numerator - Packs per outer box	50
EAN/UPC - Case	8718291195191

Essential MV MR16 Alu

Dimensional drawing



Product	D (max)	C (max)
ESS MR16 Alu 50W GU10 230V 36D 1CT	51 mm	51 mm

