



# Halogen Classic Reflector

## EcoClassic 42W E27 R80 25D 1CT/10 SRP

Philips Halogen Classic light bulbs offer the classical shapes you are used to. This new 'classic' gives high-quality light, is dimmable and starts immediately.

### Product data

General Information	
Cap-Base	E27 [ E27]
Operating Position	UNIVERSAL [ Any or Universal (U)]
Nominal Lifetime (Nom)	2000 h
Switching Cycle	8000X

Light Technical	
Beam Angle (Nom)	25 °
Luminous Flux (Rated) (Nom)	255 lm
Luminous Intensity (Max)	800 cd
Rated Beam Angle	25 °
Colour Temperature, horizontal (Nom)	2800 K
Colour Rendering Index horiz (Nom)	100
LLMF at End of Nominal Lifetime (Min)	80 %
Luminous Flux in 90° Cone (Rated)	255 lm

Operating and Electrical	
Power (Rated) (Nom)	42.0 W
Lamp Current (Nom)	0.18 A
Starting Time (Nom)	0.0 s
Warm Up Time to 60% Light (Nom)	instant full light
Power Factor (Nom)	1

Voltage (Nom)	230 V
---------------	-------

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Frosted (FR)

Approval and Application	
Energy Efficiency Label	D
Energy Consumption kWh/1000 h	42 kWh


Luminaire Design Requirements	
Cap-Base Temperature (Max)	130 °C

Product Data	
Full product code	872790083530401
Order product name	EcoClassic 42W E27 R80 25D 1CT/10 SRP
EAN/UPC - Product	8727900835304
Order code	83530401
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10

# Halogen Classic Reflector

Material Nr. (12NC)	925645444208
Net Weight (Piece)	39.500 g

## Dimensional drawing



HalClass 42W E27 230V R80 25D FR

Product	D (max)	C (max)
EcoClassic 42W E27 R80 25D 1CT/10 SRP	81 mm	112 mm

## Photometric data

Halogen: relative spectral power distribution

