

Halogen Classic P45

EcoClassic30 28W E14 230V P45 CL 1CT/20

Philips Halogen Classic light bulbs offer the classical shapes you are used to. This new 'classic' gives high-quality light, is dimmable and starts immediately.

Product data

| General Information | |
|------------------------|----------------------------------|
| Cap-Base | E14 [E14] |
| Operating Position | UNIVERSAL [Any or Universal (U)] |
| Nominal lifetime | 2,000 hour(s) |
| Switching Cycle | 8,000 |
| Rated Lifetime (Hours) | 2,000 hour(s) |
| Lighting Technology | Halogen |

| Light Technical | |
|------------------------------------|-----------|
| Luminous Flux | 370 lm |
| Correlated Color Temperature (Nom) | 2800 K |
| Luminous Efficacy (rated) (Nom) | 12.4 lm/W |
| Color rendering index (CRI) | 100 |

| Operating and Electrical | |
|---------------------------|----------------------|
| Power Consumption | 28.0 W |
| Lamp Current (Nom) | 0.12 A |
| Starting Time (Nom) | 0.0 s |
| Warm-up time to 60% light | instant full light s |
| Power Factor (Fraction) | 1 |
| Voltage (Nom) | 230 V |
| Voltage (Nom) | 230 V |

| Controls and Dimming | |
|----------------------|-----|
| Dimmable | Yes |


| Mechanical and Housing | |
|------------------------|--------------|
| Bulb Finish | Clear |
| Bulb Shape | P45 [P 45mm] |

| Approval and Application | |
|-------------------------------|--------|
| Energy Consumption kWh/1000 h | 28 kWh |

| Product Data | |
|---------------------------------|---|
| Order product name | EcoClassic30 28W E14 230V P45 CL 1CT/20 |
| Full product name | EcoClassic30 28W E14 230V P45 CL 1CT/20 |
| Full product code | 871829118364800 |
| Order code | 925648044210 |
| Material Nr. (12NC) | 925648044210 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8718291183648 |
| Numerator - Packs per outer box | 20 |
| EAN/UPC - Case | 8718291183655 |

Halogen Classic P45

Dimensional drawing



| Product | D (max) | C (max) |
|---|---------|---------|
| EcoClassic30 28W E14 230V P45 CL 1CT/20 | 46 mm | 80 mm |

