



# Halogen Classic P45

## ClassicHalo 42W E14 240V P45 CL 2PF

Philips Halogen Classic light bulbs offer the classical shapes you are used to. This new 'classic' gives high-quality light, is dimmable and starts immediately.

### Product data

General Information	
Cap-Base	E14 [E14]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen

Light Technical	
Luminous Flux	630 lm
Correlated Color Temperature (Nom)	2800 K
Luminous Efficacy (rated) (Nom)	15.0 lm/W
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	42.0 W
Lamp Current (Nom)	0.18 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	240 V
Voltage (Nom)	240 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	P45 [P 45mm]


Approval and Application	
Energy Consumption kWh/1000 h	42 kWh

Product Data	
Order product name	ClassicHalo 42W E14 240V P45 CL 2PF
Full product name	ClassicHalo 42W E14 240V P45 CL 2PF
Full product code	871829177024400
Order code	925648145503
Material Nr. (12NC)	925648145503
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291770244
Numerator - Packs per outer box	100
EAN/UPC - Case	8718291770268

## Halogen Classic P45

### Dimensional drawing



Product	D (max)	C (max)
ClassicHalo 42W E14 240V P45 CL 2PF	46 mm	80 mm

