



# Twistline GU10

## BC50 TWISTLINE GU10/FL25 12CT/6

Bright, white accent light with superior energy savings. Philips Twistline GU10 Philips Halogen Twistline MR16 with GU10 base provide bright white accent light. The twist and lock base enables easy installation and a secure fit. Suited for track and recessed lighting applications.


### Product data

General Information	
Cap-Base	GU10 [GU10]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Beam Angle (Nom)	25 degree(s)
Correlated Color Temperature (Nom)	2800 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	50 W
Starting Time (Nom)	0.0 s
Voltage (Nom)	120 V
Voltage (Nom)	120 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	MR16 [2inch/50mm]
Product Data	
Order product name	BC50 TWISTLINE GU10/FL25 12CT/6
Order code	925691836306
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	925691836306
Full product name	BC50 TWISTLINE GU10/FL25 12CT/6
EAN/UPC - Case	50046677218299
EAN/UPC - Product/Case	046677218294


Twistline GU10

Dimensional drawing



Product	D (max)	C (max)
BC50 TWISTLINE GU10/FL25 12CT/6	51 mm	53 mm

Photometric data



Light Distribution Diagram - BC50 TWISTLINE GU10/FL25 12CT/6

