



# Halogen Clickline G9

## Halogen MV Click 18W G9 230V CL 1CT

Ideal solution for small decorative luminaires. UV-block glass and safety fuse allow usage without cover glass. The compact Clickline gives crisp white light over a long lifetime.

### Product data


General information	
Cap base	G9 [ G9]
Operating position	UNIVERSAL [ Any or Universal (U)]
Nominal lifetime (nom.)	2000 h
Switching cycle	8,000X
Rated lifetime (hours)	2000 h
	Sphere
Light technical	
Luminous flux (nom.)	195 lm
Luminous flux (rated) (nom.)	204 lm
Chromaticity coordinate X (nom.)	0.452
Chromaticity coordinate Y (nom.)	0.409
Correlated Colour Temperature (Nom)	2800 K
Luminous efficacy (rated) (nom.)	11.1 lm/W
Colour rendering index (nom.)	100
LLMF at end of nominal lifetime (min.)	80 %
Operating and electrical	
Power (Rated) (Nom)	19 W
Lamp current (nom.)	0.08 A
Starting time (nom.)	0.0 s
Warm-up time to 60% light (nom.)	instant full light
Power factor (nom.)	1

Voltage (Nom)	230 V
Controls and dimming	
Dimmable	Yes
Mechanical and housing	
Lamp Finish	Clear
Bulb shape	T13 [ T 13 mm]
Approval and application	
Energy Efficiency Class	G
Energy consumption kWh/1,000 hours	19 kWh
	423243
Luminaire design requirements	
Bulb temperature (max.)	950 °C
Pinch temperature (max.)	350 °C
Product data	
Full product code	872790089577300
Order product name	Halogen MV Click 18W G9 230V CL 1CT
EAN/UPC – product	8727900895773
Order code	89577300
SAP numerator – quantity per pack	1

## Halogen Clickline G9

Numerator – packs per outer box	100
SAP material	925697744201
Copy Net Weight (Piece)	3.300 g

### Dimensional drawing



Halogen MV Click 18W G9 230V CL 1CT

Product	D (max)	L	C (max)
Halogen MV Click 18W G9 230V CL 1CT	13 mm	21.7 mm	45 mm

