



Halogen Clickline G9

Halogen Capsule 18W G9 240V 1BC/15 SRP

Ideal solution for small decorative luminaires. UV-block glass and safety fuse allow usage without cover glass. The compact Clickline gives crisp white light over a long lifetime.

Product data

General Information	
Cap-Base	G9 [G9]
Operating Position	UNIVERSAL [Any or Universal (U)]
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen

Light Technical	
Luminous Flux	204 lm
Correlated Color Temperature (Nom)	2800 K
Luminous Efficacy (rated) (Nom)	11.1 lm/W
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	18 W
Lamp Current (Nom)	0.07 A
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	240 V
Voltage (Nom)	240 V


Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T13 [T 13 mm]

Product Data	
Order product name	Halogen Capsule 18W G9 240V 1BC/15 SRP
Full product name	Halogen Capsule 18W G9 240V 1BC/15 SRP
Full product code	872790092241701
Order code	925697845505
Material Nr. (12NC)	925697845505
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900922417
Numerator - Packs per outer box	15
EAN/UPC - Case	8718696422687

Halogen Clickline G9

Dimensional drawing



Product	D (max)	L	C (max)
Halogen Capsule 18W G9 240V 1BC/15 SRP	12.75 mm	21.7 mm	44.6 mm

