



Halogen PAR

Halogen 53PAR30L/EV/FL25 120V 16/2 TP

Halogen PAR lamps reduce energy consumption without sacrificing the qualities of a traditional PAR lamp. They uniquely produce light more efficiently. They work with dimmer switches and are available in the familiar PAR20, PAR30S, PAR30L, and PAR38 shapes. Use them in existing fixtures just as you would standard halogen PAR lamps.

Product data

General Information	
Base	E26 [Single Contact Medium Screw]
Operating Position	Universal [Universal]
Main Application	Indoor Reflector
Gas Filling	GAS

Light Technical	
Beam Angle (Nom)	25 °
Initial lumen (Nom)	920 lm
Luminous Intensity (Nom)	3100 cd
Beam Description	Flood [Flood]
Luminous Flux Lamp @ 120V	920 lm
Correlated Color Temperature (Nom)	2900 K
Color Rendering Index (Nom)	100


Operating and Electrical	
Power (Rated) (Nom)	53 W
Voltage (Nom)	120 V

Mechanical and Housing	
Bulb Finish	Clear (CL)
Cap-Base Information	Brass [Brass Cap]
Bulb Material	Hard Glass
Reflector Finish	Aluminized
Filament Shape	CC-8 [Axial]

Product Data	
Order product name	Halogen 53PAR30L/EV/FL25 120V 16/2 TP
EAN/UPC - Product	50046677429367
Order code	429365
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	16
Material Nr. (12NC)	925706936305
Net Weight (Piece)	220.000 g

Halogen PAR

Dimensional drawing



Product

Halogen 53PAR30L/EV/FL25 120V 16/2 TP

PAR30L 53W E26/Brass 120V FL 25D

