



# Halogen PAR

## Halogen 53PAR30L/EVP/WFL40 120V 15/1

Halogen PAR lamps reduce energy consumption without sacrificing the qualities of a traditional PAR lamp. They uniquely produce light more efficiently. They work with dimmer switches and are available in the familiar PAR20, PAR30S, PAR30L, and PAR38 shapes. Use them in existing fixtures just as you would standard halogen PAR lamps.


### Product data

General Information	
Base	E26 [ Single Contact Medium Screw]
Operating Position	Universal [ Universal]
Main Application	Indoor Reflector
Gas Filling	GAS
Life with 3 Hour Per Day Use	2.7 a
Light Technical	
Beam Angle (Nom)	40 °
Initial lumen (Nom)	920 lm
Luminous Intensity (Nom)	950 cd
Beam Description	Wide Flood [ Wide Flood]
Correlated Color Temperature (Nom)	2790 K
Color Rendering Index (Nom)	100
Operating and Electrical	
Power (Rated) (Nom)	53 W
Voltage (Nom)	120 V
Mechanical and Housing	
Bulb Finish	Clear (CL)

Cap-Base Information	Brass [ Brass Cap]
Bulb Material	Hard Glass
Reflector Finish	Aluminized
Filament Shape	CC-8 [ Axial]
Approval and Application	
Estimated Energy Cost Per Year	6.02 \$
Product Data	
Order product name	Halogen 53PAR30L/EVP/WFL40 120V 15/1
EAN/UPC - Product	046677428952
Order code	428952
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	15
Material Nr. (12NC)	925707036302
Net Weight (Piece)	0.220 kg

# Halogen PAR

## Dimensional drawing



### Product

Halogen 53PAR30L/EVP/WFL40 120V 15/1

PAR30L 53W E26/Brass 120V WFL 40D

