



# Halogen Deco

## Halogen BC25G16-1/2C/EV/CL 120V 6/2 TP

Halogen bulbs reduce energy consumption without sacrificing the qualities of a traditional bulb. They uniquely produce light more efficiently. They work with dimmer switches and are available in the familiar G25 & G16.5 globes, bent and blunt tip candles, and flames. Use them in existing fixtures just as you would standard incandescents and your home will look great while you save energy.

### Product data

General Information	
Cap-Base	E12 [Candelabra Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,500 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,500 hour(s)
Lighting Technology	Halogen

  

Light Technical	
Luminous Flux	280 lm
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	95

  

Operating and Electrical	
Power Consumption	25 W
Lamp Current (Nom)	0.21 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Voltage (Nom)	120 V
Voltage (Nom)	120 V

Controls and Dimming	
Dimmable	Yes

  

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	G16.5 [G16.5]

  

Product Data	
Order product name	BC25G16-1/2C/EV/CL 120V 6/2 TP
Full product name	Halogen BC25G16-1/2C/EV/CL 120V 6/2 TP
Order code	420869
Material Nr. (12NC)	925707536301
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677420864
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677420869

# Halogen Deco

## Dimensional drawing

Product	D (max)	C (max)
BC25G16-1/2C/EV/CL 120V 6/2 TP	51 mm	76 mm

