



# Halogen Deco

## Halogen BC25G16-1/2C/EV/W 120V 6/2 TP

Halogen bulbs reduce energy consumption without sacrificing the qualities of a traditional bulb. They uniquely produce light more efficiently. They work with dimmer switches and are available in the familiar G25 & G16.5 globes, bent and blunt tip candles, and flames. Use them in existing fixtures just as you would standard incandescents and your home will look great while you save energy.

### Product data


General Information	
Cap-Base	E12 [ Candelabra Screw]
Operating Position	Universal [ Universal]
Nominal Lifetime (Nom)	2500 h
Switching Cycle	8000X
Light Technical	
Luminous Flux (Nom)	252 lm
Luminous Flux (Rated) (Nom)	252 lm
Correlated Color Temperature (Nom)	2700 K
Color Rendering Index (Nom)	95
Operating and Electrical	
Power (Rated) (Nom)	25 W
Lamp Current (Nom)	0.21 A
Starting Time (Nom)	0.0 s
Warm Up Time to 60% Light (Nom)	instant full light
Voltage (Nom)	120 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	White (WH)
Approval and Application	
Energy Efficiency Label (EEL)	D
Product Data	
Order product name	Halogen BC25G16-1/2C/EV/W 120V 6/2 TP
EAN/UPC - Product	50046677432237
Order code	432237
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	925707636302
Net Weight (Piece)	0.012 kg

## Halogen Deco

### Dimensional drawing

Product	D (max)	C (max)
Halogen BC25G16-1/2C/EV/W 120V 6/2 TP	51 mm	76 mm



HalClass 25W E12 120V G16.5 WH

