



Halogen Deco

Halogen 40G25/EV/CL 120V 12/1 TP

Halogen bulbs reduce energy consumption without sacrificing the qualities of a traditional bulb. They uniquely produce light more efficiently. They work with dimmer switches and are available in the familiar G25 & G16.5 globes, bent and blunt tip candles, and flames. Use them in existing fixtures just as you would standard incandescents and your home will look great while you save energy.

Product data


General information	
Base	E26 [Single Contact Medium Screw]
Operating Position	Universal [Universal]
Nominal Lifetime (Nom)	2500 h
Switching Cycle	8000X
Rated Lifetime (Hours)	2500 h
Light technical	
Initial lumen (Nom)	550 lm
Luminous Flux (Rated) (Nom)	550 lm
Correlated Color Temperature (Nom)	2800 K
Color Rendering Index (Nom)	95
Operating and electrical	
Power (Rated) (Nom)	40 W
Lamp Current (Nom)	0.33 A
Starting Time (Nom)	0.0 s
Warm Up Time to 60% Light (Nom)	instant full light
Voltage (Nom)	120 V

Controls and dimming	
Dimmable	Yes
Mechanical and housing	
Bulb Finish	Clear
Bulb Shape	G25 [G25 (G25)]
Product data	
Order product name	Halogen 40G25/EV/CL 120V 12/1 TP
EAN/UPC - Product	046677420840
Order code	420844
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	925707936301
Net Weight (Piece)	0.001 kg

Halogen Deco

Dimensional drawing

Product	D (max)	C (max)
Halogen 40G25/EV/CL 120V 12/1 TP	80 mm	115 mm



Halogen 40G25/EV/CL 120V 12/1 TP

