



Halogen Classic Reflector

EcoClassic 42W E27 E80 55D 1CT/10 SRP

Philips Halogen Classic light bulbs offer the classical shapes you are used to. This new 'classic' gives high-quality light, is dimmable and starts immediately.

Product data


General Information		Starting Time (Max)	
Cap-Base	E27 [E27]		0.0 s
Operating Position	UNIVERSAL [Any or Universal (U)]	Warm Up Time to 60% Light (Nom)	instant full light
Nominal Lifetime (Nom)	2000 h	Power Factor (Nom)	1
Life with 3 Hour Per Day Use	2 a	Voltage (Nom)	230 V
Switching Cycle	8000X	Controls and Dimming	
Light Technical		Dimmable	Yes
Beam Angle (Nom)	55 °	Mechanical and Housing	
Luminous Flux (Nom)	265 lm	Bulb Finish	Frosted (FR)
Luminous Flux (Rated) (Nom)	265 lm	Approval and Application	
Luminous Intensity (Max)	307 cd	Energy Efficiency Label	D
Rated Beam Angle	55 °	Energy Consumption kWh/1000 h	42 kWh
Colour Temperature, horizontal (Nom)	2800 K	Luminaire Design Requirements	
Luminous Efficacy (rated) (Nom)	6.3 lm/W	Cap-Base Temperature (Max)	130 °C
Colour Rendering Index horiz (Nom)	100	Product Data	
LLMF At End Of Nominal Lifetime (Nom)	85 %	Full product code	871829177096101
Luminous Flux in 90° Cone (Rated)	265 lm	Order product name	Halogen Classic E80 55D 1CT/10 SRP
Operating and Electrical		EAN/UPC - Product	8718291770961
Power (Rated) (Nom)	42 W		
Lamp Current (Nom)	0.18 A		

Halogen Classic Reflector

Order code	77096101
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	925718944203

Net Weight (Piece)	46.000 g
--------------------	----------


Dimensional drawing



HalClass 42W E27 230V E80 55D

Product	D (max)	C (max)
Halogen Classic E80 55D 1CT/10 SRP	81 mm	112 mm

Photometric data



Consumer Lamps, Halogen, Spectral power distribution

