



# Halogen Classic Reflector

## EcoClassic 42W E27 E80 55D 1CT/10 SRP

Philips Halogen Classic light bulbs offer the classical shapes you are used to. This new 'classic' gives high-quality light, is dimmable and starts immediately.

### Product data

General Information	
Cap-Base	E27 [E27]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen

Light Technical	
Beam Angle (Nom)	55 degree(s)
Luminous Flux	265 lm
Correlated Color Temperature (Nom)	2800 K
Luminous Efficacy (rated) (Nom)	6.3 lm/W
Color rendering index (CRI)	100
LLMF At End Of Nominal Lifetime (Nom)	85 %
Luminous Flux in 90° Cone (Rated)	265 lm

Operating and Electrical	
Power Consumption	42 W
Lamp Current (Nom)	0.18 A
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1

Voltage (Nom)	230 V
Voltage (Nom)	230 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	E80 [E 80mm]


Approval and Application	
Energy Consumption kWh/1000 h	42 kWh

Product Data	
Order product name	EcoClassic E80 55D 1CT/10 SRP
Full product name	EcoClassic 42W E27 E80 55D 1CT/10 SRP
Full product code	871829177096101
Order code	77096101
Material Nr. (12NC)	925718944203
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291770961
Numerator - Packs per outer box	10

# Halogen Classic Reflector

EAN/UPC - Case	8718696462775
----------------	---------------

## Dimensional drawing



Product	D (max)	C (max)
EcoClassic E80 55D 1CT/10 SRP	81 mm	112 mm

