



# Halogen Classic Reflector

## EcoClassic 28W E14 R39 45D 1CT/10 SRP

Philips Halogen Classic light bulbs offer the classical shapes you are used to. This new 'classic' gives high-quality light, is dimmable and starts immediately.

### Product data


General Information		Lamp Current (Nom)	
Cap-Base	E14 [ E14]		0.12 A
Operating Position	UNIVERSAL [ Any or Universal (U)]	Wattage Equivalent	30 W
Nominal Lifetime (Nom)	2000 h	Starting Time (Nom)	0.0 s
Life with 3 Hour Per Day Use	2 a	Warm Up Time to 60% Light (Nom)	instant full light
Switching Cycle	8000X	Power Factor (Nom)	1
		Voltage (Nom)	230 V
Light Technical		Controls and Dimming	
Beam Angle (Min)	45	Dimmable	Yes
Beam Angle (Nom)	45 °		
Luminous Flux (Nom)	150 lm	Mechanical and Housing	
Luminous Flux (Rated) (Nom)	150 lm	Bulb Finish	Frosted (FR)
Luminous Intensity (Max)	200 cd		
Rated Beam Angle	45 °	Approval and Application	
Colour Temperature, horizontal (Nom)	2800 K	Energy Efficiency Label	D
Luminous Efficacy (rated) (Nom)	5.35 lm/W	Energy Consumption kWh/1000 h	28 kWh
Colour Rendering Index horiz (Nom)	100		
LLMF At End Of Nominal Lifetime (Nom)	80 %	Luminaire Design Requirements	
Luminous Flux in 90° Cone (Rated)	150 lm	Cap-Base Temperature (Max)	120 °C
Operating and Electrical		Product Data	
Power (Rated) (Nom)	28.0 W	Full product code	871829175721401

# Halogen Classic Reflector

Order product name	EcoClassic 28W E14 R39 45D 1CT/10 SRP
EAN/UPC - Product	8718291757214
Order code	75721401
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10

Material Nr. (12NC)	925719044204
Net Weight (Piece)	0.016 kg

## Dimensional drawing



HalClass 28W E14 230V R39 45D FR

Product	D (max)	C (max)
EcoClassic 28W E14 R39 45D 1CT/10 SRP	40 mm	75.5 mm

## Photometric data

