



Halogen Classic Reflector

EcoClassic 28W E14 R39 45D 1CT/10 SRP

Philips Halogen Classic light bulbs offer the classical shapes you are used to. This new 'classic' gives high-quality light, is dimmable and starts immediately.

Product data

General Information	
Cap-Base	E14 [E14]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen

Light Technical	
Beam Angle (Nom)	45 degree(s)
Luminous Flux	150 lm
Correlated Color Temperature (Nom)	2800 K
Luminous Efficacy (rated) (Nom)	5.35 lm/W
Color rendering index (CRI)	100
LLMF At End Of Nominal Lifetime (Nom)	80 %
Luminous Flux in 90° Cone (Rated)	150 lm

Operating and Electrical	
Power Consumption	28.0 W
Lamp Current (Nom)	0.12 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s

Power Factor (Fraction)	1
Voltage (Nom)	230 V
Voltage (Nom)	230 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	R39 [R 39mm]


Approval and Application	
Energy Consumption kWh/1000 h	28 kWh

Product Data	
Order product name	EcoClassic 28W E14 R39 45D 1CT/10 SRP
Full product name	EcoClassic 28W E14 R39 45D 1CT/10 SRP
Full product code	871829175721401
Order code	925719044204
Material Nr. (12NC)	925719044204
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291757214

Halogen Classic Reflector

Numerator - Packs per outer box	10
EAN/UPC - Case	8718696469071

Dimensional drawing



Product	D (max)	C (max)
EcoClassic 28W E14 R39 45D 1CT/10 SRP	40 mm	75.5 mm

