



# Brilliantline Dichroic

## Brilliantline Dichroic EC 20W GU4 12V 30D 1CT/10X5F

Low-voltage, xenon gas-filled halogen burner with axial filament optically positioned in a dichroic coated glass reflector


### Product data

General Information	
Cap-Base	GU4 [GU4]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	4,000 hour(s)
Switching Cycle	16,000
Rated Lifetime (Hours)	4,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Beam Angle (Nom)	30 degree(s)
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	100
Luminous Flux in 90° Cone (Rated)	205 lm
Operating and Electrical	
Power Consumption	20 W
Lamp Current (Nom)	1.7 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	Instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	12 V
Voltage (Nom)	12 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	MR11 [1.375inch/35mm]
Approval and Application	
Energy Consumption kWh/1000 h	21 kWh
Product Data	
Order product name	Brill EC 20W GU4 12V 30D 1CT/10X5F
Full product name	Brilliantline Dichroic EC 20W GU4 12V 30D 1CT/10X5F
Full product code	871869959137300
Order code	59137300
Material Nr. (12NC)	925721617102
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699591373
Numerator - Packs per outer box	50
EAN/UPC - Case	8718699591380

Brilliantline Dichroic

Dimensional drawing



Product	D (max)	C (max)
Brill EC 20W GU4 12V 30D 1CT/10X5F	35 mm	40 mm

