



# Capsules LV 3,000 h

## Caps 3000h 35W GY6.35 12V CL 1CT/10x10F

Low-voltage halogen capsule. Ideal solution for small decorative luminaires. The UV-block glass and low-pressure filling allow usage without cover glass. The compact halogen capsule delivers crisp white light over a long lifetime.


### Product data

General Information	
Cap base	GY6.35 [ GY6.35]
Operating position	UNIVERSAL [ Any/Universal]
Nominal lifetime (nom.)	3000 h
Switching cycle	12000X
Light Technical	
Luminous flux (nom.)	766 lm
Luminous flux (rated) (nom.)	766 lm
Correlated colour temperature (nom.)	3100 K
Luminous efficacy (rated) (nom.)	21.9 lm/W
Color rendering index (nom.)	100
Operating and Electrical	
Power (Rated) (Nom)	35.0 W
Lamp current (nom.)	2.917 A
Starting time (nom.)	0.0 s
Warm-up time to 60% light (nom.)	instant full light s
Power factor (nom.)	1
Voltage (Nom)	12 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb finish	Clear (CL)
Approval and Application	
Energy efficiency label (EEL)	B
Energy Consumption kWh/1000 h	35 kWh
Luminaire Design Requirements	
Bulb temperature (max.)	900 °C
Pinch temperature (max.)	350 °C
Product Data	
Full product code	871869682783300
Order product name	Caps 3000h 35W GY6.35 12V CL 1CT/10x10F
EAN/UPC – product	8718696827833
Order code	82783300
Numerator – quantity per pack	1
Numerator – packs per outer box	100
Material no. (12NC)	925723717101
Net weight (piece)	0.003 kg

## Capsules LV 3,000 h

### Dimensional drawing



Product	D (max)	L	C (max)
Caps 3000h 35W GY6.35 12V CL 1CT/10x10F	12 mm	30 mm	44 mm

EcoHalo Capsule Gy6.35 12v35w CL B3000

