



MV Halogen Oven Capsules



Caps OV 25W G9 230V 1CT/20

Halogen capsules ideal as a replacement lamp for many specific oven types.
Resistant to high temperatures, perfectly fitting oven application.

Product data


General Information	
Cap base	G9 [G9]
Operating position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 h
Rated Lifetime (Hours)	2,000 h
Lighting Technology	Halogen
Flux measurement reference	Sphere
Light Technical	
Luminous Flux	250 lm
Chromaticity Coordinate X (Nom)	0.468
Chromaticity Coordinate Y (Nom)	0.412
Correlated Colour Temperature	2650 K
Colour rendering index (CRI)	100
Operating and Electrical	
Power Consumption	26 W
Lamp current (nom.)	0.11 A
Starting time (nom.)	0.0 s
Power Factor (Fraction)	1
Voltage (nom.)	230 V

Voltage (nom.)	230 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	T11 [T 11 mm]
Approval and Application	
Energy Efficiency Class	G
Energy consumption kWh/1,000 hours	26 kWh
EPREL registration number	423260
Product Data	
Order product name	Caps OV 25W G9 230V 1CT/20
Full product name	Caps OV 25W G9 230V 1CT/20
Full EOC	871869961321100
Order code	61321100
Material no. (12 NC)	925723944201
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718699613211

MV Halogen Oven Capsules

Numerator – packs per outer box	20
EAN/UPC – Case	8718699613228

Dimensional drawing



Product	D (max)	C (max)
Caps OV 25W G9 230V 1CT/20	12.75 mm	44.6 mm

