



MV Halogen Oven Capsules

Caps OV 25W G9 230V 1CT/20

Halogen capsules ideal as a replacement lamp for many specific oven types. Resistant to high temperatures, perfectly fitting oven application.


Product data

General Information	
Cap base	G9 [G9]
Operating position	UNIVERSAL [Any/Universal]
Nominal lifetime (nom.)	2000 h
Light Technical	
Luminous flux (nom.)	260 lm
Correlated colour temperature (nom.)	2650 K
Operating and Electrical	
Power (Rated) (Nom)	25 W
Lamp current (nom.)	0.11 A
Starting time (nom.)	0.0 s
Power factor (nom.)	1
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb finish	Clear (CL)

Approval and Application	
Energy efficiency label (EEL)	D
Luminaire Design Requirements	
Pinch temperature (max.)	350 °C
Product Data	
Full product code	871869961321100
Order product name	Caps OV 25W G9 230V 1CT/20
EAN/UPC – product	8718699613211
Order code	61321100
Numerator – quantity per pack	1
Numerator – packs per outer box	20
Material no. (12NC)	925723944201
Net weight (piece)	0.004 kg

MV Halogen Oven Capsules

Dimensional drawing



Product	D (max)	C (max)
Caps OV 25W G9 230V 1CT/20	12.75 mm	44.6 mm

Halogen oven capsule G9 230V 25W

