



Reflector diam 50 mm

Refl 40W E14 230V NR50 30D 3FO/30

Reflector lamps based on advanced spotlighting technology

Product data

General Information	
Cap-Base	E14 [E14]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Beam Angle (Nom)	30 degree(s)
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	40 W
Voltage (Nom)	230 V
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes


Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	NR50 [NR 50mm]
Product Data	
Order product name	Refl 40W E14 230V NR50 30D 3FO/30
Full product name	Refl 40W E14 230V NR50 30D 3FO/30
Full product code	871150032709378
Order code	926000002524
Material Nr. (12NC)	926000002524
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500327093
Numerator - Packs per outer box	30
EAN/UPC - Case	8711500344786

Reflector diam 50 mm

Dimensional drawing

Product	D
Refl 40W E14 230V NR50 30D 3FO/30	50 mm

Photometric data



Light Distribution Diagram - Refl 40W E14 230V NR50 30D 3FO/30

