



# Standard Lustre P45 frosted

## STAN 60W E14 230V P45 FR 1CT/10X10F

Spherical vacuum- or gas-filled incandescent lamps with white or inside-frosted glass bulb and E-base


### Product data

General Information	
Cap-Base	E14 [ E14]
Operating Position	UNIVERSAL [ Any or Universal (U)]
Nominal Lifetime (Nom)	1000 h
Light Technical	
Luminous Flux (Nom)	650 lm
Colour Rendering Index horiz (Nom)	100
Operating and Electrical	
Power (Rated) (Nom)	60 W
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted (FR)
Cap-Base Information	na [ -]

Filament Shape	-
Approval and Application	
Energy Efficiency Label	F
Energy Consumption kWh/1000 h	60 kWh
Product Data	
Full product code	871150006757950
Order product name	Standard 60W E14 230V P45 FR 1CT/10X10F
EAN/UPC - Product	8711500067579
Order code	06757950
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	100
Material Nr. (12NC)	926000003857
Net Weight (Piece)	0.015 kg
ILCOS Code	IBP/F-60-230-E14-45

## Standard Lustre P45 frosted

### Dimensional drawing



LUS STD 60W E14 230V P45 FR

Product	D	C (max)
Standard 60W E14 230V P45 FR 1CT/10X10F	45 mm	78 mm

