



Reflector diam 63 mm

Refl 60W E27 230V NR63 30D FR 1CT/30

Reflector lamps based on advanced spotlighting technology


Product data

| General Information | |
|-----------------------------|----------------------------------|
| Cap-Base | E27 [E27] |
| Operating Position | UNIVERSAL [Any or Universal (U)] |
| Nominal lifetime | 1,000 hour(s) |
| Rated Lifetime (Hours) | 1,000 hour(s) |
| Lighting Technology | Incandescent |
| Light Technical | |
| Beam Angle (Nom) | 30 degree(s) |
| Color rendering index (CRI) | 100 |
| Operating and Electrical | |
| Power Consumption | 60 W |
| Voltage (Nom) | 230 V |
| Voltage (Nom) | 230 V |
| Controls and Dimming | |
| Dimmable | Yes |

| Mechanical and Housing | |
|---------------------------------|--------------------------------------|
| Bulb Finish | Frosted |
| Bulb Shape | NR63 [NR 63mm] |
| Product Data | |
| Order product name | Refl 60W E27 230V NR63 30D FR 1CT/30 |
| Full product name | Refl 60W E27 230V NR63 30D FR 1CT/30 |
| Full product code | 871150004366578 |
| Order code | 926000005918 |
| Material Nr. (12NC) | 926000005918 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500043665 |
| Numerator - Packs per outer box | 30 |
| EAN/UPC - Case | 8711500343994 |


Reflector diam 63 mm

Dimensional drawing



| Product | D |
|--------------------------------------|-------|
| Refl 60W E27 230V NR63 30D FR 1CT/30 | 63 mm |

Photometric data



Light Distribution Diagram - Refl 60W E27 230V NR63 30D FR 1CT/30

