



Standard Lustre P45 clear

STAN 40W E27 230V P45 CL 1CT/10X10F

Spherical vacuum- or gas-filled incandescent lamps with a clear glass bulb and E-base


Product data

General Information	
Cap-Base	E27 [E27]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal Lifetime (Nom)	1000 h
Light Technical	
Luminous Flux (Nom)	390 lm
Colour Rendering Index horiz (Nom)	100
Operating and Electrical	
Power (Rated) (Nom)	40 W
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear (CL)

Cap-Base Information	na [-]
Filament Shape	-
Approval and Application	
Energy Efficiency Label	E
Product Data	
Full product code	871150001188650
Order product name	Standard 40W E27 230V P45 CL 1CT/10X10F
EAN/UPC - Product	8711500011886
Order code	01188650
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	100
Material Nr. (12NC)	926000006412
Net Weight (Piece)	14.550 g
ILCOS Code	IBP/C-40-230-E27-45

Standard Lustre P45 clear

Dimensional drawing



LUS STD 40W E27 230V P45 CL

Product	D	C (max)
Standard 40W E27 230V P45 CL 1CT/10X10F	45 mm	73 mm

