



Standard Lustre P45 clear

STAN 40W E14 230V P45 CL 1CT/10X10F


Spherical vacuum- or gas-filled incandescent lamps with a clear glass bulb and E- or B-base

Product data

General Information		Cap-base information	
Cap base	E14 [E14]	Cap-base information	na [-]
Operating position	UNIVERSAL [Any or Universal (U)]	Filament shape	-
Nominal lifetime (nom.)	1000 h	Bulb shape	P45 [P 45mm]
Rated lifetime (hours)	1000 h		
Light Technical		Product Data	
Luminous flux (nom.)	405 lm	Full product code	871150001186250
Colour rendering index (nom.)	100	Order product name	Standard 40W E14 230V P45 CL 1CT/10X10F
		EAN/UPC – product	8711500011862
Operating and Electrical		Order code	01186250
Power (Rated) (Nom)	40 W	SAP numerator – quantity per pack	1
Voltage (Nom)	230 V	Numerator – packs per outer box	100
		SAP material	926000006511
Controls and Dimming		SAP net weight (piece)	0.015 kg
Dimmable	Yes	ILCOS code	IBP/C-40-230-E14-45
Mechanical and Housing			
Lamp Finish	Clear		

Standard Lustre P45 clear

Dimensional drawing



Product	D	C (max)
Standard 40W E14 230V P45 CL 1CT/10X10F	45 mm	78 mm

LUS STD 40W E14 230V P45 CL

