



# Standard Lustre P45 frosted

## STAN 40W E27 230V P45 FR 1CT/10X10F


Spherical vacuum- or gas-filled incandescent lamps with white or inside-frosted glass bulb and E- or B-base

### Product data

General information		Cap-base information	
Cap base	E27 [ E27]	Cap-base information	na [-]
Operating position	UNIVERSAL [ Any or Universal (U)]	Filament shape	-
Nominal lifetime (nom.)	1000 h	Bulb shape	P45 [ P 45mm]
Rated lifetime (hours)	1000 h	<b>Product data</b>	
<b>Light technical</b>		Full product code	871150001122050
Luminous flux (nom.)	390 lm	Order product name	Standard 40W E27 230V P45 FR 1CT/10X10F
Colour rendering index (nom.)	100	EAN/UPC – product	8711500011220
<b>Operating and electrical</b>		Order code	01122050
Power (Rated) (Nom)	40 W	SAP numerator – quantity per pack	1
Voltage (Nom)	230 V	Numerator – packs per outer box	100
<b>Controls and dimming</b>		SAP material	926000007412
Dimmable	Yes	Copy Net Weight (Piece)	20.150 g
<b>Mechanical and housing</b>		ILCOS code	IBP/F-40-230-E27-45
Lamp Finish	Frosted		

## Standard Lustre P45 frosted

### Dimensional drawing



Standard 40W E27 230V P45 FR 1CT/10X10F

Product	D	C (max)
Standard 40W E27 230V P45 FR 1CT/10X10F	45 mm	73 mm

