



Standard Lustre P45 frosted

STAN 40W E27 230V P45 FR 1CT/10X10F


Spherical vacuum- or gas-filled incandescent lamps with white or inside-frosted glass bulb and E-base

Product data

General Information		Cap-Base Information	
Cap-Base	E27 [E27]	na [-]	
Operating Position	UNIVERSAL [Any or Universal (U)]	Filament Shape	-
Nominal Lifetime (Nom)	1000 h	Approval and Application	
Light Technical		Energy Efficiency Label	E
Luminous Flux (Nom)	390 lm	Product Data	
Colour Rendering Index horiz (Nom)	100	Full product code	871150001122050
Operating and Electrical		Order product name	Standard 40W E27 230V P45 FR 1CT/10X10F
Power (Rated) (Nom)	40 W	EAN/UPC - Product	8711500011220
Voltage (Nom)	230 V	Order code	01122050
Controls and Dimming		Numerator - Quantity Per Pack	1
Dimmable	Yes	Numerator - Packs per outer box	100
Mechanical and Housing		Material Nr. (12NC)	926000007412
Bulb Finish	Frosted (FR)	Net Weight (Piece)	20.150 g
		ILCOS Code	IBP/F-40-230-E27-45

Standard Lustre P45 frosted

Dimensional drawing



LUS STD 40W E27 230V P45 FR

Product	D	C (max)
Standard 40W E27 230V P45 FR 1CT/10X10F	45 mm	73 mm

