



Standard Lustre P45 frosted

Stan 60W E27 230V P45 FR 1CT/10X10F

Spherical vacuum- or gas-filled incandescent lamps with white or inside-frosted glass bulb and E- or B-base

Product data

General Information	
Cap-Base	E27 [E27]
Operating Position	S90 [Standing +/-90D or Base Down (BDH)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	640 lumen
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	60 W
Voltage (Nom)	230 V
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	P45 [P 45mm]
Approval and Application	
Energy Consumption kWh/1000 h	60 kWh
Product Data	
Full product code	871869658996000
Order product name	Stan 60W E27 230V P45 FR 1CT/10X10F
Order code	926000010908
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	100
Material Nr. (12NC)	926000010908
Full product name	Stan 60W E27 230V P45 FR 1CT/10X10F
EAN/UPC - Case	8718696589984
EAN/UPC - Product/Case	8718696589960

Standard Lustre P45 frosted

Dimensional drawing



Product	D	C (max)
Stan 60W E27 230V P45 FR 1CT/10X10F	45 mm	73 mm

