



MR16

BC-50MRC16/FL 6/3 TP

Philips Halogen MR16 lamps provide a bright white light for accent lighting. They make it easy to optimize the look and feel of your brand, your merchandise, and the shoppers experience, with lower operating costs.


Product data

General Information	
Cap-Base	GU5.3 [GU5.3]
Philips Code	14600
Operating Position	Universal [Universal]
ANSI Code Halogen	EXN
Nominal Lifetime (Nom)	2000 h
Switching Cycle	8000X
Light Technical	
Beam Angle (Nom)	36 °
Luminous Intensity (Max)	1200 cd
Rated Beam Angle	36 °
Correlated Color Temperature (Nom)	3000 K
Color Rendering Index (Nom)	100
Operating and Electrical	
Power (Rated) (Nom)	50 W
Lamp Current (Nom)	4.17 A
Starting Time (Nom)	0.0 s
Voltage (Nom)	12 V

Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy Efficiency Label (EEL)	B
Energy Consumption kWh/1000 h	53 kWh
Luminaire Design Requirements	
Cap-Base Temperature (Max)	250 °C
Product Data	
Order product name	BC-50MRC16/FL 6/3 TP
EAN/UPC - Product	50046677151206
Order code	151209
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	926000850009
Net Weight (Piece)	0.032 kg
ILCOS Code	HRGI-50-12-GU5.3-50/36

MR16

Dimensional drawing



Fighter 14600 50W GU5.3 12V MR16 36D

Product	D (max)	C (max)
BC-50MRC16/FL 6/3 TP	51 mm	46 mm

