



Accentline

Accentline 50W 4000h GU5.3 12V 36D 1CT/10X5F

Low-voltage halogen burner in glass reflector. Ideal solution for small decorative luminaires, putting your objects in the spotlight. Dichroic coating prevents heat transmission onto the object.

Product data

| General Information | |
|----------------------------|----------------------------------|
| Cap-Base | GU5.3 [GU5.3] |
| Operating Position | UNIVERSAL [Any or Universal (U)] |
| Nominal lifetime | 4,000 hour(s) |
| Switching Cycle | 16,000 |
| Rated Lifetime (Hours) | 4,000 hour(s) |
| Lighting Technology | Halogen |
| Life to 50% Failures (Nom) | 4,000 hour(s) |


| Light Technical | |
|------------------------------------|--------------|
| Beam Angle (Nom) | 36 degree(s) |
| Luminous Flux | 680 lm |
| Correlated Color Temperature (Nom) | 3000 K |
| Color rendering index (CRI) | 100 |
| Luminous Flux in 90° Cone (Rated) | 680 lm |

| Operating and Electrical | |
|---------------------------|----------------------|
| Power Consumption | 50 W |
| Starting Time (Nom) | 0.0 s |
| Warm-up time to 60% light | Instant full light s |
| Voltage (Nom) | 12 V |
| Voltage (Nom) | 12 V |

| Controls and Dimming | |
|-------------------------------|-------------------|
| Dimmable | Yes |
| Mechanical and Housing | |
| Bulb Shape | MR16 [2inch/50mm] |
| Approval and Application | |
| Energy Consumption kWh/1000 h | 53 kWh |

| Product Data | |
|---------------------------------|--|
| Order product name | Accent 50W 4000h GU5.3 12V 36D 1CT/10X5F |
| Full product name | Accentline 50W 4000h GU5.3 12V 36D 1CT/10X5F |
| Full product code | 871869658845100 |
| Order code | 58845100 |
| Material Nr. (12NC) | 926000850063 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8718696588451 |
| Numerator - Packs per outer box | 50 |
| EAN/UPC - Case | 8718696588475 |

Dimensional drawing



| Product | D (max) | C (max) |
|--|---------|---------|
| Accent 50W 4000h GU5.3 12V 36D 1CT/10X5F | 51 mm | 46 mm |

