



Accentline

Accentline 50W 4000h GU5.3 12V 36D 1CT/10X5F

Low-voltage halogen burner in glass reflector. Ideal solution for small decorative luminaires, putting your objects in the spotlight. Dichroic coating prevents heat transmission onto the object.


Product data

General information	
Cap base	GU5.3 [GU5.3]
Operating position	UNIVERSAL [Any or Universal (U)]
Life to 50% failures (nom.)	4000 h
Nominal lifetime (nom.)	4000 h
Switching cycle	16,000X
Rated lifetime (hours)	4000 h
Light technical	
Beam Angle (Nom)	36 °
Luminous flux (nom.)	680 lm
Luminous intensity (max.)	1500 cd
Rated beam angle	36 °
Correlated Colour Temperature (Nom)	3000 K
Colour rendering index (nom.)	100
Luminous flux in 90° cone (rated)	680 lm
Operating and electrical	
Power (Rated) (Nom)	50 W
Starting time (nom.)	0.0 s
Warm-up time to 60% light (nom.)	Instant full light s
Voltage (Nom)	12 V

Controls and dimming	
Dimmable	Yes
Mechanical and housing	
Bulb shape	MR16 [2inch/50mm]
Approval and application	
Energy consumption kWh/1,000 hours	53 kWh
Product data	
Full product code	871869658845100
Order product name	Accentline 50W 4000h GU5.3 12V 36D 1CT/10X5F
EAN/UPC – product	8718696588451
Order code	58845100
SAP numerator – quantity per pack	1
Numerator – packs per outer box	50
SAP material	926000850063
Net Weight (Piece)	0.006 kg

Accentline


Dimensional drawing



Product	D (max)	C (max)
Accentline 50W 4000h GU5.3 12V 36D 1CT/10X5F	51 mm	46 mm

Accentline 50W 4000h GU5.3 12V 36D 1CT/10X5F

Photometric data



Consumer Lamps, Halogen, Spectral power distribution

