



# Accentline

## Accentline 50W 4000h GU5.3 12V 36D 1CT/10X5F

Low-voltage halogen burner optically positioned in a glass reflector with and without front glass

### Product data

General Information	
Cap-Base	GU5.3
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	4,000 hour(s)
Switching Cycle	16,000
Rated Lifetime (Hours)	4,000 hour(s)
Lighting Technology	Halogen
Life to 50% Failures (Nom)	4,000 hour(s)

Light Technical	
Beam Angle (Nom)	36 degree(s)
Luminous Flux	680 lm
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	100
Luminous Flux in 90° Cone (Rated)	680 lm

Operating and Electrical	
Power Consumption	50 W
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	Instant full light s
Voltage (Nom)	12 V
Voltage (Nom)	12 V


Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	MR16

Approval and Application	
Energy Consumption kWh/1000 h	53 kWh

Product Data	
Order product name	Accent 50W 4000h GU5.3 12V 36D 1CT/10X5F
Full product name	Accentline 50W 4000h GU5.3 12V 36D 1CT/10X5F
Full product code	871869658845100
Order code	58845100
Material Nr. (12NC)	926000850063
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696588451
Numerator - Packs per outer box	50
EAN/UPC - Case	8718696588475

Dimensional drawing



Product	D (max)	C (max)
Accent 50W 4000h GU5.3 12V 36D 1CT/10X5F	51 mm	46 mm

