



Accentline

Accentline 50W 4000h GU5.3 12V 36D 1CT/10X5F

Low-voltage halogen burner optically positioned in a glass reflector with and without front glass

Product data

General Information	
Cap-Base	GU5.3 [GU5.3]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	4000 h
Nominal Lifetime (Nom)	4000 h
Switching Cycle	16000X

Light Technical	
Beam Angle (Nom)	36 °
Luminous Flux (Nom)	680 lm
Luminous Intensity (Max)	1500 cd
Rated Beam Angle	36 °
Colour Temperature, horizontal (Nom)	3000 K
Colour Rendering Index horiz (Nom)	100
Luminous Flux in 90° Cone (Rated)	680 lm

Operating and Electrical	
Power (Rated) (Nom)	50 W
Starting Time (Nom)	0.0 s
Warm Up Time to 60% Light (Nom)	instant full light s
Voltage (Nom)	12 V

Controls and Dimming	
Dimmable	Yes

Approval and Application	
Energy Efficiency Label	B
Energy Consumption kWh/1000 h	53 kWh

Product Data	
Full product code	871869658845100
Order product name	Accentline 50W 4000h GU5.3 12V 36D 1CT/ 10X5F
EAN/UPC - Product	8718696588451
Order code	58845100
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	50
Material Nr. (12NC)	926000850063
Net Weight (Piece)	0.006 kg

Accentline

Dimensional drawing



MR16 4000h 12V 50W 36D GU5.3

Product	D (max)	C (max)
Accentline 50W 4000h GU5.3 12V 36D 1CT/10X5F	51 mm	46 mm

Photometric data

